


96F Single Jacket Single Armoured Cable

Cable Design

IEC/EN 60794-3-10



- not to scale -

- **Central strength member (CSM):** glass fibre reinforced plastic rod (FRP) with coating when needed.
- **Tube:** thermoplastic material, containing 12 optical fibres and filled with a suitable water tightness compound.
- **Stranding:** the required number of elements (tubes or fillers) are SZ stranded around the central strength member.
- **Core wrapping:** water swellable tape (dry core).
- **Armour:** corrugated steel tape. 2 ripcords beneath.
- **Outer Sheath:** HDPE.

Technical data

No. of Fibres				96
Design (Elements × Fibres per Tube)				8×12
Loose Tube / Filler - nominal Ø	mm			2.0
CSM/sheath nominal diameter	mm			2.5/3.5
Outer sheath nominal thickness	mm			1.6
Cable nominal Diameter	mm			12.5
Cable Weight (±10%)	kg / km			142
Min. bending radius	mm	Without Tension 10 × Cable-Ø	Under Maximum Tension 20 × Cable-Ø	
Temperature range	°C	Installation -10 -> +60;	Transport. & Storage -40 -> +70 ;	Operation -40 -> +70

Please refer to our General Installation, Safety & Handling recommendations before handling.

Main characteristics

Test	Standard	Value	Sanction*
Max. Installation Tension	IEC 60794-1-2-E1	2700N	fibre strain ≤ 0.6%, Δα reversible
Crush	IEC 60794-1-2-E3	2200N / 100mm	Δα ≤ 0.1 dB, cable integrity
Temperature Cycling	IEC 60794-1-2-F1	-40 -> +70°C	Δα ≤ 0.05 dB/km
Water Penetration	IEC 60794-1-2-F5C	sample=3m, water=1m	No water leakage after 24 hours

* values for single-mode fibres, all optical measurements performed at 1550 nm.

Optical Characteristics

See the attached cabled optical fibre data sheet.

Identification

Fibre Colours

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	blue	orange	green	brown	grey	white	red	black	yellow	violet	pink	aqua

Loose Tube and filler Colours:

Tube No.	1	2	3	4	5	6	7	8	9	10	11	12
Tube Colour	blue	orange	green	brown	grey	white	red	black	yellow	violet	pink	aqua

All fillers are black.

Sheath Colour:

The outer sheath colour is black.

Sheath Marking:

The outer sheath is marked in 1 meter intervals as follows:

PRYSMIAN <Year of manufacture> <Fiber Count & Fiber type> ARMOURED CABLE XXXXM

Logistic

Packing:

Wooden drums with protection.

Delivery Lengths:

Standard delivery length is 4 km with a tolerance of $\pm 5\%$.

© PrysmianGroup 2024, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.